

# **DSPA AEROSOL GENERATORS**

12-1, 12-2, 12-5



#### FEATURES:

- Exceptional effective non-toxic fire extinguishing agent
- Uniquely easy to install and Maintain
- Certified according to EN 15276-1, ISO 15779, UL 2775 and BRL K23001
- Approved by EPA for SNAP listing
- Ecologically safe and environmentally friendly (O.D.P.=0, G.W.P.=0)
- Very cost efficient
- Available with electric starter (e) or built-in thermocord (t) (DSPA 12-5 only with thermocord)

#### Description

DSPA aerosol generators can be used as a part of a highly effective fixed extinguishing system. A DSPA generator is non-pressurized and is installed inside a room or compartment that requires protection. After activation, an aerosol cloud is generated, which expands volumetrically, flooding the space and extinguishing the fire. The DSPA generators are mainly designed for use in normally unoccupied and unoccupied areas; in occupied areas, the DSPA generators can be used on condition that a 30 seconds pre-alarm is installed. The DSPA generators are effective on class A, B, C and F fires.

#### Application

The DSPA generators 12-5, 12-1 and 12-2 are recommended for the protection of small objects, such as electrical cabinets and panels.

Model	12-5	12-1	12-2
Part Number	100029 (t)	100020 (e) 100025 (t)	100021 (e) 100026 (t)
Dimensions	Ø80 x 16 mm	Ø100 x 20 mm	Ø100 x 28 mm
Total weight	92 g	100 g	150 g
Compound weight	5 g	15 g	30 g
Volume coverage A(CW) + 30% safety	0,05 m³	0,15 m³	0,29 m³
Discharge time	5-7 sec	9-11 sec	13-15 sec
Activation, current	Built-in starter, 1.3A (e) or built-in thermocord (t)		
Operating conditions	-40°C to 75°C/ Up to 95% RH		
Colour	Standard RAL 3000, other colours upon request		
Min. distance for persons(75°C) from discharge outlet 250 mm Min. distance for combustible	75 75 Temperature [°C]		75 Temperature [°C]
material(200°C) from discharge outlet 100 mm	10 30 80 Distance from discharge outlet[mm]		20 80 150
Min. distance for construction structures(400°C) from discharge outlet 50 mm			Distance from discharge outlet[mm]
₩ ₩ № ₩ ₩ ₩ ₩ ₩ ₩ ₩		Data Seri Vers Date	sion: 2.3

### Specifications

## More information:

DSPA.nl Hogelandseweg 30 6545 AC Nijmegen The Netherlands T. +31 (0) 24 35 22 573 E info@dspa.nl www.dspa.nl